

CAT Powered Used Truck: Engine Checklist

Stock # _____ VIN _____ Eng. Model _____ Eng. S/N _____

Item	Results
<ul style="list-style-type: none"> <input type="checkbox"/> Verify existing coverage package <input type="checkbox"/> Complete inspection for Advantage: Change oil and fuel filter with genuine Cat Parts Take Scheduled Oil Sampling (S*O*S) <input type="checkbox"/> Access original owner maintenance records <input type="checkbox"/> Download "Lifetime" and "Fleet Trip" information to verify actual miles and driving history 	<ul style="list-style-type: none"> ⇒ Current miles: _____ mi. ⇒ Delivery date: _____ ⇒ Coverage type: _____ ⇒ Coverage: _____ yrs./ _____ mi. ⇒ Oil change interval: _____ mi. ⇒ Repairs:
<ul style="list-style-type: none"> <input type="checkbox"/> Flash in latest software version – consider up-rate rating <input type="checkbox"/> Reset customer parameters <input type="checkbox"/> Run dyno test <input type="checkbox"/> Take Scheduled Oil Sampling (S*O*S) <input type="checkbox"/> Identify appropriate coverage program 	<div style="display: flex; align-items: center;"> <div style="writing-mode: vertical-rl; transform: rotate(180deg); font-weight: bold; margin-right: 10px;">Engine Electronics</div> <ul style="list-style-type: none"> ⇒ Total miles: _____ mi. ⇒ Average fuel economy: _____ mi/gal. ⇒ Average road speed: _____ mi/hr. ⇒ Percent idle time: _____ % ⇒ Original software date: _____ / _____ ⇒ Original rating: _____ hp, _____ lb-ft ⇒ Transmission capability: _____ lb-ft ⇒ New software date: _____ / _____ ⇒ New rating: _____ hp, _____ lb-ft </div>
<ul style="list-style-type: none"> <input type="checkbox"/> Provide new owner with CAT truck engine owner Web Site address: http://mycattruckengines.cat.com (see back cover for detailed information) <input type="checkbox"/> Provide correct Operation & Maintenance Manual of engine 	<ul style="list-style-type: none"> ⇒ Dyno results: Horsepower: _____ Boost: _____ psi ⇒ Oil sample results: